

Standard Put-Up Reference Guide

Put-Up #	Putup Description	Total Footage
001	1000 FT	1000
002	500 FT	500
003	250 FT	250
004	200 FT	200
005	100 FT	100
007	50 FT	50
008	25 FT	25
010	2500 FT	2500
011	2000 FT	2000
013	5000 FT	5000
015	125 FT	125
016	150 FT	150
017	70 FT	70
018	65 FT	65
019	60 FT	60
020	40 FT	40
021	BOX 1000 FT	1000
022	BOX 500 FT	500
024	35 FT	35
025	32 FT	32
026	24 FT	24
028	16 FT	16
030	BOX 328 FT	328
032	EACH	1
033	328 FT	328
038	PACKAGE	1
059	40x6 IN	20
060	36x6 IN	18
061	32x6 IN	16
062	28x6 IN	14
063	24x6 IN	12
064	20x6 IN	10
065	16x6 IN	8
066	14x6 IN	7
067	12x6 IN	6
068	10x6 IN	5
069	8x6 IN	4
070	5x6 IN	2.5

071	4x6 IN	2
072	3x6 IN	1.5
073	2x6 IN	1
074	1x6 IN	0.5
076	1C PC/PKG	100
078	25 PC/PKG	25
080	10 PC/PKG	10
082	250 PC/PKG	250
083	500 PC/PKG	500
100	250x4 FT	1000
103	25x4 FT	100
105	5x4 FT	20
107	2x4 FT	8
114	10x2 FT	20
147	1000x1 IN	83.33
171	2000x4 FT	8000
180	48 IN BULK	1
194	6 IN BULK	1
199	BULK FT	1
204	2x500 FT	1000
205	3x1000 FT	3000
207	125x4 FT	500
212	3000 FT	3000
257	36 FT	36
270	14 FT	14
309	4000 FT	4000
312	3280 FT	3280
317	21x6 IN	10.50
318	25x6 IN	12.50
319	15x6 IN	7.50
320	9x6 IN	4.50
321	164 FT	164
322	1250 FT	1250
324	3500 FT	3500
326	100 FT UK	100
327	305 METERS	1000
328	7000 FT	7000
500	MFG BULK	1
990	BULK FT	1
991	EACH	1