

Belden PDU Specification

9BA2-241090

Description:

Non-Surge, 20A, 208V, Vertical, (24) IEC C13, 10 ft power cord with L6-20P



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	208V
3.	Current	20A
4.	VA per Input (Load Capacity)	3.3kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	None
7.	Switch	No
8.	Power Cable Wire Gauge	12/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L6-20P Twistlock
11.	Receptacle/Socket Type #1	IEC C13
12.	Quantity on Face #1	24
13.	Style #1	Banks of 4
14.	Maximum Output per Receptacle/Socket #1	15A per receptacle bank
15.	Voltage per Receptacle/Socket #1	208V
16.	Continuous Operating Temperature Range	10-45C / 50-113F
17.	Heavy Steel -Black Powder Coat	Yes

Belden PDU Specification



9BA2-241090

18.	Configuration	66in / 1682mm Vertical Rackmount
19.	7938 Vertical Mounting Bracket Kit	Yes
20.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
21.	Made in the USA	Yes
22.	Product Warranty	5-year Limited Warranty
23.	Certification/Agency Approvals	NOM-003-SCFI-2000
24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (LxWxD)	66.25in x 1.72in x 1.61in
27.	Shipped Weight	13lbs (5.9kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____