

Belden PDU Specification

Part #: 9BF1-061006

Description:

Basic, Standard, 15A, 120V, Horizontal, (6) NEMA 5-15R, breakered, 10 ft power cord with 5-15P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	15A
4.	VA per Input (Load Capacity)	1.4kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	15A Thermal Breaker
7.	Switch	No
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	14/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA 5-15P
12.	Receptacle/Socket Type #1	NEMA 5-15R
13.	- Quantity on Rear	6
14.	- Quantity per Breaker	6
15.	- Style	Duplex
16.	- Maximum Output per Receptacle/Socket	15A
17.	- Voltage per Receptacle/Socket	120V
18.	Continuous Operating Temperature Range	10-45C / 50-113F

Belden PDU Specification



Part #: 9BF1-061006

19.	Heavy Steel - Powder Coat Finish	Black
20.	Configuration	19 in / 435 mm Horizontal Rackmount
21.	Flush Mount	Yes
22.	Made in the USA	Yes
23.	Product Warranty	Five Year
24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
27.	Shipped Weight	6lbs (2.72kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____