

Belden PDU Specification

Part #: 9BF1-101002

Description:

Basic, Surge, 15A, 120V, Horizontal, (10) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Black Powder Coat.



Specification:

| | | |
|-----|--|------------------------|
| 1. | Quantity Of Inputs | 1 |
| 2. | Voltage | 120V |
| 3. | Current | 15A |
| 4. | VA per Input (Load Capacity) | 1.4kW |
| 5. | Frequency | 50/60 Hz |
| 6. | Over Current Protection | 15A Thermal Breaker |
| 7. | Switch | Yes |
| 8. | Indicators - LED(s) | 1 - Power ON Green LED |
| 9. | Power Cable Wire Gauge | 14/3 |
| 10. | Power Cable Length | 10ft |
| 11. | Plug Type | NEMA 5-15P |
| 12. | Receptacle/Socket Type #1 | NEMA 5-15R |
| 13. | - Quantity on Rear | 10 |
| 14. | - Quantity per Breaker | 10 |
| 15. | - Style | Duplex |
| 16. | - Maximum Output per Receptacle/Socket | 15A |
| 17. | - Voltage per Receptacle/Socket | 120V |
| 18. | Joule Rating | 720 |
| 19. | Maximum Clamping Voltage | 340V |

Belden PDU Specification



Part #: 9BF1-101002

| | | |
|-----|--|--|
| 20. | Response Time | < 5 nanoseconds |
| 21. | Technology Used | Super MOVs |
| 22. | Surge Indicator Red LED | Yes |
| 23. | Continuous Operating Temperature Range | 10-45C / 50-113F |
| 24. | Heavy Steel - Powder Coat Finish | Black |
| 25. | Configuration | 19 in / 435 mm Horizontal Rackmount |
| 26. | Flush Mount | Yes |
| 27. | Made in the USA | Yes |
| 28. | Product Warranty | Lifetime (Surge Suppression - 5 Years) |
| 29. | Connected Equipment Warranty | Five Year - \$5000 |
| 30. | Certification/Agency Approvals | RoHS Compliant |
| 31. | Certification/Agency Approvals | UL & c-UL Listed 60950 |
| 32. | Chassis Dimensions (HxWxD) | 1.72in x 17in x 3.75in |
| 33. | Shipped Weight | 6lbs (2.72kg) |

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____