

Belden PDU Specification

Part #: 9BG1-201001

Description:

Basic, Standard, 20A, 120V, Vertical, (20) NEMA 5-20R, 10 ft power cord with 5-20P, Black Powder Coat.



Specification:

| | | |
|-----|--|------------------------------------|
| 1. | Quantity Of Inputs | 1 |
| 2. | Voltage | 120V |
| 3. | Current | 20A |
| 4. | VA per Input (Load Capacity) | 1.9kW |
| 5. | Frequency | 50/60 Hz |
| 6. | Over Current Protection | None |
| 7. | Switch | No |
| 8. | Power Cable Wire Gauge | 12/3 |
| 9. | Power Cable Length | 10ft |
| 10. | Plug Type | NEMA 5-20P |
| 11. | Receptacle/Socket Type #1 | NEMA 5-20R |
| 12. | - Quantity on Face | 20 |
| 13. | - Style | Individual - In-Line |
| 14. | - Maximum Output per Receptacle/Socket | 20A |
| 15. | - Voltage per Receptacle/Socket | 120V |
| 16. | Center to Center Receptacle Spacing | 3.0 |
| 17. | Continuous Operating Temperature Range | 10-25C / 50-77F |
| 18. | Heavy Steel - Powder Coat Finish | Black |
| 19. | Configuration | 66 in / 1683 mm Vertical Rackmount |
| 20. | 7938 Vertical Mounting Bracket Kit | Yes |
| 21. | Vertical/Panel Mount Brackets (MJ) | Yes |
| 22. | Made in the USA | Yes |
| 23. | Product Warranty | Five Year |
| 24. | Certification/Agency Approvals | RoHS Compliant |

Belden PDU Specification



Part #: 9BG1-201001

| | | |
|-----|--------------------------------|--------------------------|
| 25. | Certification/Agency Approvals | UL & c-UL Listed 60950 |
| 26. | Chassis Dimensions (LxWxD) | 66.25in x 1.25in x 1.1in |
| 27. | Shipped Weight | 8lbs (3.63kg) |

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____