

# Belden PDU Specification

**Part #: 9BG2-101003**

## Description:

Basic, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with L5-20P, Black Powder Coat.



## Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	20A
4.	VA per Input (Load Capacity)	1.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	20A Thermal Breaker
7.	Switch	Yes
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	12/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA L5-20P Twistlock
12.	Receptacle/Socket Type #1	NEMA 5-20R
13.	Quantity on Rear #1	10

# Belden PDU Specification



**Part #: 9BG2-101003**

14.	Quantity per Breaker #1	10
15.	Style #1	Duplex
16.	Maximum Output per Receptacle/Socket #1	20A
17.	Voltage per Receptacle/Socket #1	120V
18.	Continuous Operating Temperature Range	10-45C / 50-113F
19.	Heavy Steel - Powder Coat Finish	Black
20.	Configuration	19in / 435mm Horizontal Rackmount
21.	Flush Mount	Yes
22.	Made in the USA	Yes
23.	Product Warranty	5-year Limited Warranty
24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
27.	Shipped Weight	6lbs (2.72kg)

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_