

Belden PDU Specification

Part #: 9BG2-121008

Description:

Basic, Standard, 20A, 120V, Horizontal, (12) NEMA 5-20R, breakered, 10 ft power cord with L5-20P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	20A
4.	VA per Input (Load Capacity)	1.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	20A Thermal Breaker
7.	Switch	No
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	12/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA L5-20P Twistlock
12.	Receptacle/Socket Type #1	NEMA 5-20R
13.	- Quantity on Face	2
14.	- Quantity on Rear	10
15.	- Quantity per Breaker	12
16.	- Style	Duplex
17.	- Maximum Output per Receptacle/Socket	20A
18.	- Voltage per Receptacle/Socket	120V
19.	Continuous Operating Temperature Range	10-45C / 50-113F

Belden PDU Specification



Part #: 9BG2-121008

20.	Heavy Steel - Powder Coat Finish	Black
21.	Configuration	19 in / 435 mm Horizontal Rackmount
22.	Flush Mount	Yes
23.	Made in the USA	Yes
24.	Product Warranty	Five Year
25.	Certification/Agency Approvals	RoHS Compliant
26.	Certification/Agency Approvals	UL & c-UL Listed 60950
27.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
28.	Shipped Weight	6lbs (2.72kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____