

Belden PDU Specification

9BG2-201004

Description:

Basic, 20A, 120V, Vertical, (20) NEMA 5-20R, 10 ft power cord with L5-20P, Black Powder Coat. Non-surge



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	20A
4.	VA per Input (Load Capacity)	1.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	None
7.	Switch	No
8.	Power Cable Wire Gauge	12/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L5-20P Twistlock
11.	Receptacle/Socket Type #1	NEMA 5-20R
12.	Quantity on Face #1	20
13.	Center to Center Receptacle Spacing	3.0
14.	Style #1	Individual - In-Line
15.	Maximum Output per Receptacle/Socket #1	20A
16.	Voltage per Receptacle/Socket #1	120V
17.	Continuous Operating Temperature Range	10-25C / 50-77F
18.	Heavy Steel - Powder Coat Finish	Black
19.	Configuration	66in / 1682mm Vertical Rackmount
20.	7938 Vertical Mounting Bracket Kit	Yes
21.	Vertical/Panel Mount Brackets (MJ)	Yes
22.	Made in the USA	Yes
23.	Product Warranty	Five Year
24.	Certification/Agency Approvals	RoHS Compliant

Belden PDU Specification



9BG2-201004

25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (LxWxD)	66.25in x 1.25in x 1.1in
27.	Shipped Weight	8lbs (3.63kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____