

# Belden PDU Specification

**Part #: 9LG1-101004**

**Description:**

Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with 5-20P, Power - Local (A, V, W, PF)  
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.



**Specification:**

1.	Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2.	Monitoring Level 1	Aggregate - Total Unit Monitoring
3.	Quantity Of Inputs	1
4.	Voltage	120V
5.	Current	20A
6.	VA per Input (Load Capacity)	1.9kW

# Belden PDU Specification

## Part #: 9LG1-101004

---

7.	Frequency	50/60 Hz
8.	Over Current Protection	20A Thermal Breaker
9.	Switch	Yes
10.	Indicators - LED(s)	1 - Power ON Green LED
11.	Power Cable Wire Gauge	12/3
12.	Power Cable Length	10ft
13.	Plug Type	NEMA 5-20P
14.	Receptacle/Socket Type #1	NEMA 5-20R
15.	Quantity on Rear #1	10
16.	Quantity per Breaker #1	10
17.	Style #1	Duplex
18.	Maximum Output per Receptacle/Socket #1	20A
19.	Voltage per Receptacle/Socket #1	120V
20.	Joule Rating	720
21.	UL 1449 Rating (500A)	330V
22.	Clamping Level	< 315V
23.	Response Time	< 5 nanoseconds
24.	Technology Used	Super MOVs
25.	Surge Indicator Red LED	Yes
26.	Continuous Operating Temperature Range	10-45C / 50-113F
27.	Heavy Steel - Powder Coat Finish	Black
28.	Configuration	19in / 435mm Horizontal Rackmount

---

# Belden PDU Specification



**Part #: 9LG1-101004**

---

29.	Flush Mount	Yes
30.	Made in the USA	Yes
31.	Product Warranty	5-year limited warranty
32.	Certification/Agency Approvals	RoHS Compliant
33.	Certification/Agency Approvals	UL & c-UL Listed 60950
34.	Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
35.	Shipped Weight	8lbs (3.63kg)

---

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_