

Belden PDU Specification

Part #: 9SO5-080001

Description:

Switched, Outlet Level Monitoring, + Environmental Monitoring -- 20A, 120/208V, Horizontal, (8) Locking IEC C13, C20, Input, per Circuit/Breaker and per Outlet power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet connectivity. Local LCD display. Black Powder Coat.



Specification:

1.	Monitoring	Input, per Circuit/Breaker and per Outlet power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet connectivity. Local LCD display.
2.	Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
3.	Monitoring Level 2	Circuit / Breaker Monitoring (kWh, W, VA, PF, V, A)
4.	Monitoring Level 3	Outlet Monitoring (kWh, W, VA, PF, V, A)
5.	Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
6.	Quantity Of Inputs	1
7.	Voltage	120V or 208V
8.	Current	20A
9.	VA per Input (Load Capacity)	1.9 or 3.3kW
10.	Frequency	50/60 Hz
11.	Over Current Protection	None
12.	Switch	No
13.	Indicators - LED(s)	8
14.	Activity LED	1
15.	Idle LED	1
16.	Power LED	1
17.	Scrolling Digital Display	Yes
18.	Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
19.	Receptacle/Socket Type #1	Locking IEC C13

Belden PDU Specification



Part #: 9SO5-080001

20.	- Quantity on Rear	8
21.	- Style	Individual
22.	- Maximum Output per Receptacle/Socket	15A
23.	- Voltage per Receptacle/Socket	120V or 208V
24.	Internal RMS Voltage Sensor	Yes
25.	Internal RMS Current Sensor	Yes
26.	Network Connection	Ethernet via RJ45
27.	Network Protocols Supported and Data Access Formats	ARP, IPv4, IPv6, ICMP, ICMPv6, NDP, TCP, UDP, DNS, HTTP, HTTPS, SMTP, SMTPS, DHCP, SNMP (v1/v2c/v3), Syslog, SSH, LDAP, JSON API, Web GUI, CLI, JSON datalog, CSV datalog
28.	Reboot Button	Yes
29.	Remote Sensor RJ Connection Jacks	2
30.	RSD - Optional Remote Display Jack	Yes
31.	Continuous Operating Temperature Range	10-45C / 50-113F
32.	Heavy Steel - Powder Coat Finish	Black
33.	Configuration	19 in / 435 mm Horizontal Rackmount
34.	Adjustable Mount Brackets	Yes
35.	Made in the USA	Yes
36.	Product Warranty	Five Year
37.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
38.	Certification/Agency Approvals	RoHS Compliant
39.	Certification/Agency Approvals	UL & c-UL Listed 60950
40.	Chassis Dimensions (HxWxD)	1.72in x 17.1in x 8.5in
41.	Shipped Weight	5lbs (2.27kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____