

# Belden PDU Specification

**Part #: 9BI2-241001**

## Description:

Basic, Standard, 20A, 120/208V WYE, 3 Phase, Vertical, (24) NEMA 5-20R, 10 ft power cord with L21-20P, Black Powder Coat.



## Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120/208V WYE
3.	Current	20A x 3 Phase WYE
4.	VA per Input (Load Capacity)	5.7kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	None
7.	Switch	No
8.	Power Cable Wire Gauge	12/5
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L21-20P Twistlock
11.	Receptacle/Socket Type #1	NEMA 5-20R
12.	- Quantity on Face	24
13.	- Quantity per Phase	8
14.	- Style	Duplex
15.	- Maximum Output per Receptacle/Socket	20A
16.	- Voltage per Receptacle/Socket	120V
17.	Continuous Operating Temperature Range	10-45C / 50-113F
18.	Heavy Steel - Powder Coat Finish	Black
19.	Configuration	66 in / 1683 mm Vertical Rackmount
20.	7938 Vertical Mounting Bracket Kit	Yes
21.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
22.	Made in the USA	Yes
23.	Product Warranty	Five Year
24.	Certification/Agency Approvals	RoHS Compliant

# Belden PDU Specification



## Part #: 9BI2-241001

---

25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
27.	Shipped Weight	15lbs (6.8kg)

---

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_