

Belden PDU Specification

Part #: 9BJ2-241003

Description:

Basic, Standard, 30A, 120/208V WYE, 3 Phase, Vertical, (24) NEMA 5-20R, breakered, 10 ft power cord with L21-30P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120/208V WYE
3.	Current	30A x 3 Phase WYE
4.	VA per Input (Load Capacity)	8.6kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(3) 20A Double Pole Magnetic Breakers
7.	Switch	Breaker/Switch Combination
8.	Power Cable Wire Gauge	10/5
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L21-30P Twistlock
11.	Receptacle/Socket Type #1	NEMA 5-20R
12.	- Quantity on Face	24
13.	- Quantity per Breaker and Phase	8
14.	- Style	Duplex
15.	- Maximum Output per Receptacle/Socket	20A
16.	- Voltage per Receptacle/Socket	120V
17.	Continuous Operating Temperature Range	10-45C / 50-113F
18.	Heavy Steel - Powder Coat Finish	Black
19.	Configuration	66 in / 1682 mm Vertical Rackmount
20.	7938 Vertical Mounting Bracket Kit	Yes
21.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
22.	Made in the USA	Yes
23.	Product Warranty	Five Year

Belden PDU Specification



Part #: 9BJ2-241003

24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
27.	Doghouse (D)	1.44in
28.	Shipped Weight	17lbs (7.71kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____