

Belden PDU Specification

Part #: 9PB2-101003

Description:

Monitored, Unit Level EC, Upgradeable, 30A, 208V, Horizontal, (10) Locking IEC C13, breakered, 10 ft power cord with L6-30P, Input power monitoring with breaker level current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display. Black Powder Coat.



Specification:

Monitoring	Input power monitoring with breaker level current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 2	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
VLC Support	Yes
Quantity Of Inputs	1
Voltage	208V
Current	30A

Belden PDU Specification



Part #: 9PB2-101003

VA per Input (Load Capacity)	4.9kW
Frequency	50/60 Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Power Entry Location	Left Rear
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Rear	10
- Quantity per Breaker	5
- U-Lock Color ID	2 Circuit = Orange, Green
- Style	Individual
- Voltage per Receptacle/Socket	208V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Network Connection	Dual 10/100Mbps Ethernet
Network Protocols Supported and Data Access Formats	HTTP, HTTPS (TLS 1.2), SMTP, SMTPS (TLS 1.2), ICMP, DHCP, IPv4, IPv6, Syslog, SNMP v1/v2c/v3, JSON, JSON API, RSTP
IP Reset Button	Yes
Hard Reboot Button	Yes
Remote Sensor RJ Connection Jacks	1 (Supports up to 4 Sensors)

Belden PDU Specification



Part #: 9PB2-101003

Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in
Shipped Weight	12lbs (5.44kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____