



EDAF1021, EDAF1121, EDAF1022, EDAF1122	230 V 50 Hz; In 0,18 A; PN 45 W
EDAF1041, EDAF1141, EDAF1042, EDAF1142	230 V 50 Hz; In 0,36 A; PN 90 W
EDAF1061, EDAF1161, EDAF1062, EDAF1162	230 V 50 Hz; In 0,54 A; PN 140 W