

Belden PDU Specification

9BH2-121004

Description:

Non-Surge, 30A, 120V, Horizontal, (12) NEMA 5-20R, breakered, 10 ft power cord with L5-30P



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	30A
4.	VA per Input (Load Capacity)	2.8kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(2) 20A Single Pole Magnetic Breakers
7.	Switch	Breaker/Switch Combination
8.	Power Cable Wire Gauge	10/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L5-30P Twistlock
11.	Receptacle/Socket Type #1	NEMA 5-20R
12.	Quantity on Face #1	2
13.	Quantity on Rear #1	10

Belden PDU Specification



9BH2-121004

14.	Quantity per Breaker #1	6
15.	Style #1	Duplex
16.	Maximum Output per Receptacle/Socket #1	20A
17.	Voltage per Receptacle/Socket #1	120V
18.	Continuous Operating Temperature Range	10-45C / 50-113F
19.	Heavy Steel -Black Powder Coat	Yes
20.	Configuration	19in / 435mm Horizontal Rackmount
21.	Adjustable Mount Brackets	Yes
22.	Made in the USA	Yes
23.	Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
24.	Certification/Agency Approvals	NOM-003-SCFI-2000
25.	Certification/Agency Approvals	RoHS Compliant
26.	Certification/Agency Approvals	UL & c-UL Listed 60950
27.	Chassis Dimensions (HxWxD)	1.72in x 17in x 6.50in
28.	Shipped Weight	8lbs (3.63kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____