

Belden PDU Specification

9BJ2-121001

Description:

Basic, 30A, 120/208V WYE, 3 Phase, Vertical, (12) NEMA L5-20R, breakered, 10 ft power cord with L21-30P



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120/208V WYE
3.	Current	30A x 3 Phase WYE
4.	VA per Input (Load Capacity)	8.6kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(3) 20A Double Pole Magnetic Breakers
7.	Switch	Breaker/Switch Combination
8.	Power Cable Wire Gauge	10/5
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L21-30P Twistlock
11.	Receptacle/Socket Type #1	NEMA L5-20R
12.	Quantity on Face #1	12
13.	Quantity per Breaker and Phase #1	4
14.	Style #1	Individual
15.	Maximum Output per Receptacle/Socket #1	20A
16.	Voltage per Receptacle/Socket #1	120V
17.	Continuous Operating Temperature Range	10-45C / 50-113F
18.	Heavy Steel - Powder Coat Finish	Black
19.	Configuration	66in / 1683mm Vertical Rackmount
20.	7938 Vertical Mounting Bracket Kit	Yes
21.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
22.	Made in the USA	Yes
23.	Product Warranty	5-year limited warranty
24.	Certification/Agency Approvals	RoHS Compliant

Belden PDU Specification



9BJ2-121001

25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
27.	Doghouse (D)	1.44in
28.	Shipped Weight	17lbs (7.71kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____