

Belden PDU Specification

Part #: 9BG1-101001

Description:

Basic, Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with 5-20P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	20A
4.	VA per Input (Load Capacity)	1.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	20A Thermal Breaker
7.	Switch	Yes
8.	Indicators - LED(s)	1 - Power ON Green LED
9.	Power Cable Wire Gauge	12/3
10.	Power Cable Length	10ft
11.	Plug Type	NEMA 5-20P
12.	Receptacle/Socket Type #1	NEMA 5-20R
13.	- Quantity on Rear	10
14.	- Quantity per Breaker	10
15.	- Style	Duplex
16.	- Maximum Output per Receptacle/Socket	20A
17.	- Voltage per Receptacle/Socket	120V
18.	Joule Rating	720
19.	Maximum Clamping Voltage	340V

Belden PDU Specification



Part #: 9BG1-101001

20.	Response Time	< 5 nanoseconds
21.	Technology Used	Super MOVs
22.	Surge Indicator Red LED	Yes
23.	Continuous Operating Temperature Range	10-45C / 50-113F
24.	Heavy Steel - Powder Coat Finish	Black
25.	Configuration	19 in / 435 mm Horizontal Rackmount
26.	Flush Mount	Yes
27.	Made in the USA	Yes
28.	Product Warranty	Five Year
29.	Connected Equipment Warranty	Five Year - \$5000
30.	Certification/Agency Approvals	RoHS Compliant
31.	Certification/Agency Approvals	UL & c-UL Listed 60950
32.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
33.	Shipped Weight	7lbs (3.18kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____