

Belden PDU Specification

9BB2-241090

Description:

Non-Surge, 30A, 208V, Vertical, (24) IEC C13, breakered, 10 ft power cord with L6-30P



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	208V
3.	Current	30A
4.	VA per Input (Load Capacity)	4.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(4) 15A Thermal Breakers
7.	Switch	No
8.	Power Cable Wire Gauge	10/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L6-30P Twistlock
11.	Receptacle/Socket Type #1	IEC C13
12.	Quantity on Face #1	24
13.	Quantity per Breaker Pair #1	12
14.	Style #1	Banks of 4
15.	Maximum Output per Receptacle/Socket #1	15A per receptacle bank
16.	Voltage per Receptacle/Socket #1	208V
17.	Continuous Operating Temperature Range	10-45C / 50-113F

Belden PDU Specification



9BB2-241090

18.	Heavy Steel -Black Powder Coat	Yes
19.	Configuration	66in / 1682mm Vertical Rackmount
20.	7938 Vertical Mounting Bracket Kit	Yes
21.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
22.	Made in the USA	Yes
23.	Product Warranty	5-year Limited Warranty
24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
26.	Chassis Dimensions (LxWxD)	66.25in x 1.72in x 1.61in
27.	Shipped Weight	13lbs (5.9kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____