

Belden PDU Specification

Part #: 9BG2-121007

Description:

Basic, Standard, 20A, 120V, Horizontal, (12) NEMA 5-20R, power switch, breakered, 10 ft power cord with L5-20P, Black Powder Coat.



Specification:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	2

Belden PDU Specification



Part #: 9BG2-121007

- Quantity on Rear	10
- Quantity per Breaker	12
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19 in / 483 mm Horizontal Rackmount
Flush Mount	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
Shipped Weight	6lbs (2.72kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____