

Belden PDU Specification

Part #: 9BG2-241003

Description:

Basic, Standard, 20A, 120V, Vertical, (24) NEMA 5-20R, 10 ft power cord with L5-20P, Black Powder Coat.



Specification:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	24
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black

Belden PDU Specification



Part #: 9BG2-241003

Configuration	66 in / 1683 mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	13lbs (5.9kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____