

Belden PDU Specification

Part #: 9LA2-061001

Description:

Basic, 20A, 208V, Horizontal, (6) NEMA L6-20R, 10 ft power cord with L6-20P, Power - Local (A, V, W, PF)
Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.



Specification:

1.	Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2.	Monitoring Level 1	Aggregate - Total Unit Monitoring
3.	Quantity Of Inputs	1
4.	Voltage	208V
5.	Current	20A
6.	VA per Input (Load Capacity)	3.3kW
7.	Frequency	50/60 Hz
8.	Over Current Protection	None
9.	Switch	No

Belden PDU Specification

Part #: 9LA2-061001

10.	Power Cable Wire Gauge	12/3
11.	Power Cable Length	10ft
12.	Plug Type	NEMA L6-20P Twistlock
13.	Receptacle/Socket Type #1	NEMA L6-20R
14.	Quantity on Rear #1	6
15.	Style #1	Individual
16.	Maximum Output per Receptacle/Socket #1	20A
17.	Voltage per Receptacle/Socket #1	208V
18.	Continuous Operating Temperature Range	10-45C / 50-113F
19.	Heavy Steel - Powder Coat Finish	Black
20.	Configuration	19in / 435mm Horizontal Rackmount
21.	19in Recess Mount	Yes
22.	Made in the USA	Yes
23.	Product Warranty	5-year limited warranty
24.	Certification/Agency Approvals	RoHS Compliant
25.	Certification/Agency Approvals	UL & c-UL Listed 60950
26.	Chassis Dimensions (HxWxD)	3.39in x 17in x 6in
27.	Shipped Weight	14lbs (6.35kg)

Belden PDU Specification



Part #: 9LA2-061001

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____