

Belden PDU Specification

Part #: 9LG1-101002

Description:

Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, breakered, 10 ft power cord with 5-20P, Current - Local

Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input , Aggregate - Total Unit Monitoring



Specification:

1	Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2	Monitoring Level 1	Aggregate - Total Unit Monitoring
3	Quantity Of Inputs	1
4	Voltage	120V
5	Current	20A
6	VA per Input (Load Capacity)	1.9kW
7	Frequency	50/60 Hz
8	Over Current Protection	20A Thermal Breaker
9	Switch	No
10	Indicators - LED(s)	1 - Power ON Green LED
11	Power Cable Wire Gauge	12/3
12	Power Cable Length	10ft
13	Plug Type	NEMA 5-20P
14	Receptacle/Socket Type #1	NEMA 5-20R
15	Quantity on Rear #1	10
16	Quantity per Breaker #1	10
17	Style #1	Duplex
18	Maximum Output per Receptacle/Socket #1	20A
19	Voltage per Receptacle/Socket #1	120V
26	Heavy Steel -Black Powder Coat	Yes
27	Configuration	19in / 435mm Horizontal Rackmount

Belden PDU Specification



Part #: 9LG1-101002

28	Flush Mount	Yes
29	Made in the USA	Yes
30	Product Warranty	5-year limited warranty
31	Certification/Agency Approvals	RoHS Compliant
32	Certification/Agency Approvals	UL & c-UL Listed 60950
33	Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
34	Shipped Weight	8lbs (3.63kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized

Customer Signature: _____ Date: _____