

Belden PDU Specification

Part #: 9LF1-101001

Description:

Metered, Standard, 15A, 120V, Horizontal, (10) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Power - Local (A, V, W, PF)
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input.
 Black Powder Coat.



Specification:

1.	Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2.	Monitoring Level 1	Aggregate - Total Unit Monitoring
3.	Quantity Of Inputs	1
4.	Voltage	120V
5.	Current	15A
6.	VA per Input (Load Capacity)	1.4kW
7.	Frequency	50/60 Hz
8.	Over Current Protection	15A Thermal Breaker
9.	Switch	Yes
10.	Indicators - LED(s)	1 - Power ON Green LED

Belden PDU Specification



Part #: 9LF1-101001

11.	Power Cable Wire Gauge	14/3
12.	Power Cable Length	10ft
13.	Plug Type	NEMA 5-15P
14.	Receptacle/Socket Type #1	NEMA 5-15R
15.	- Quantity on Rear	10
16.	- Quantity per Breaker	10
17.	- Style	Duplex
18.	- Maximum Output per Receptacle/Socket	15A
19.	- Voltage per Receptacle/Socket	120V
20.	Continuous Operating Temperature Range	10-45C / 50-113F
21.	Heavy Steel - Powder Coat Finish	Black
22.	Configuration	19 in / 435 mm Horizontal Rackmount
23.	Flush Mount	Yes
24.	Made in the USA	Yes
25.	Product Warranty	Five Year
26.	Certification/Agency Approvals	RoHS Compliant
27.	Certification/Agency Approvals	UL & c-UL Listed 60950
28.	Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
29.	Shipped Weight	7lbs (3.18kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____