

# Belden PDU Specification

**Part #: 9LG1-101001**

## Description:

Metered, Standard, 20A, 120V, Horizontal, (10) NEMA 5-20R, breakered, 10 ft power cord with 5-20P, Power - Local (A, V, W, PF)  
 Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.



## Specification:

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW

# Belden PDU Specification



## Part #: 9LG1-101001

Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Rear	10
- Quantity per Breaker	10
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19 in / 483 mm Horizontal Rackmount
Flush Mount	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in

# Belden PDU Specification



**Part #: 9LG1-101001**

Shipped Weight	8lbs (3.63kg)
----------------	---------------

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_