

Belden PDU Specification

Part #: 9PH2-241007

Description:

Metered, Upgradeable, 30A, 120V, Vertical, (24) NEMA 5-20R, breakered, 10 ft power cord with L5-30P, Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the mobile app. Black Powder Coat.



Specification:

1.	Monitoring	Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the mobile app.
2.	Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
3.	VLC Support	Yes
4.	Quantity Of Inputs	1
5.	Voltage	120V
6.	Current	30A
7.	VA per Input (Load Capacity)	2.8kW
8.	Frequency	50/60 Hz
9.	Over Current Protection	(2) 20A Single Pole Magnetic Breakers
10.	Switch	Breaker/Switch Combination
11.	Scrolling / Rotatable Digital Display	Yes
12.	Power Cable Wire Gauge	10/3
13.	Power Cable Length	10ft
14.	Power Entry Location	Bottom Front
15.	Plug Type	NEMA L5-30P Twistlock
16.	Receptacle/Socket Type #1	NEMA 5-20R
17.	- Quantity on Face	24
18.	- Style	Duplex
19.	- Voltage per Receptacle/Socket	120V
20.	Internal RMS Voltage Sensor	Yes
21.	Internal RMS Current Sensor	Yes
22.	Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F

Belden PDU Specification



Part #: 9PH2-241007

23.	Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
24.	Heavy Steel - Powder Coat Finish	Black
25.	Configuration	66 in / 1683 mm Vertical Rackmount
26.	7938 Vertical Mounting Bracket Kit	Yes
27.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
28.	Made in the USA	Yes
29.	Product Warranty	Five Year
30.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
31.	Certification/Agency Approvals	RoHS Compliant
32.	Certification/Agency Approvals	UL & c-UL Listed 60950
33.	Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
34.	Shipped Weight	15lbs (6.8kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____