

Belden PDU Specification

Part #: 9BK2-421001

Description:

Basic, Upgradeable, 30A, 208V DELTA, 3 Phase, Vertical, (36) IEC C13, (6) IEC C19, breakered, 10 ft power cord with L15-30P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.



Specification:

1.	Monitoring	No Monitoring (Upgradeable with IMD module)
2.	Quantity Of Inputs	1
3.	Voltage	208V Delta
4.	Current	30A x 3 Phase DELTA
5.	VA per Input (Load Capacity)	8.6kW
6.	Frequency	50/60 Hz
7.	Over Current Protection	(3) 20A Double Pole Magnetic Breakers
8.	Switch	Breaker/Switch Combination
9.	Power Cable Wire Gauge	10/4
10.	Power Cable Length	10ft
11.	Power Entry Location	Bottom Front
12.	Plug Type	NEMA L15-30P Twistlock
13.	Combined Total Receptacle/Socket Quantity	42
14.	Receptacle/Socket Type #1	IEC C13
15.	Quantity on Face #1	36
16.	Quantity per Breaker and Phase Combination #1	12

Belden PDU Specification

Part #: 9BK2-421001

17.	Style #1	Banks of 6
18.	Voltage per Receptacle/Socket #1	208V
19.	Receptacle/Socket Type #2	IEC C19
20.	Quantity on Face #2	6
21.	Quantity per Breaker and Phase Combination #2	2
22.	Style #2	Individual
23.	Voltage per Receptacle/Socket #2	208V
24.	Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F
25.	Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
26.	Heavy Steel - Powder Coat Finish	Black
27.	Configuration	72in / 1832mm Vertical Rackmount
28.	7938 Vertical Mounting Bracket Kit	Yes
29.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
30.	Made in the USA	Yes
31.	Product Warranty	Five Year
32.	Certification/Agency Approvals	FCC Part 15 Class A Conformance
33.	Certification/Agency Approvals	RoHS Compliant

Belden PDU Specification



Part #: 9BK2-421001

34.	Certification/Agency Approvals	UL & c-UL Listed 60950
35.	Chassis Dimensions (LxWxD)	72in x 2in x 2in
36.	Shipped Weight	17lbs (7.71kg)

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized Customer Signature: _____ Date: _____