

Belden PDU Specification

Part #: 9LA2-241001

Description:

Basic, 20A, 208V, Vertical, (24) IEC C13, 10 ft power cord with L6-20P, Current - Local

Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.



Specification:

Monitoring	Current - Local
1.	Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2. Monitoring Level 1	Aggregate - Total Unit Monitoring
3. Quantity Of Inputs	1
4. Voltage	208V
5. Current	20A
6. VA per Input (Load Capacity)	3.3kW
7. Frequency	50/60 Hz
8. Over Current Protection	None
9. Switch	No
10. Power Cable Wire Gauge	12/3

Belden PDU Specification

Part #: 9LA2-241001

11.	Power Cable Length	10ft
12.	Plug Type	NEMA L6-20P Twistlock
13.	Receptacle/Socket Type #1	IEC C13
14.	Quantity on Face #1	24
15.	Style #1	Banks of 4
16.	Maximum Output per Receptacle/Socket #1	15A per receptacle bank
17.	Voltage per Receptacle/Socket #1	208V
18.	Continuous Operating Temperature Range	10-45C / 50-113F
19.	Heavy Steel - Powder Coat Finish	Black
20.	Configuration	66in / 1682mm Vertical Rackmount
21.	7938 Vertical Mounting Bracket Kit	Yes
22.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
23.	Made in the USA	Yes
24.	Product Warranty	5-year limited warranty
25.	Certification/Agency Approvals	RoHS Compliant
26.	Certification/Agency Approvals	UL & c-UL Listed 60950
27.	Chassis Dimensions (LxWxD)	66.25in x 1.72in x 1.61in
28.	Shipped Weight	13lbs (5.9kg)

Belden PDU Specification



Part #: 9LA2-241001

To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____